

Ground Rod Splice, Heavy Duty




Heavy duty connections were originally developed to be used on reclaimed cable. The heavy duty connections use a larger size connection cavity in the mold and a larger size welding material than the equivalent standard duty connection.

The larger size welding material supplies extra BTU's to melt the heavy oxide coating on the conductor and to overcome some severe field conditions. Heavy duty connections eliminate cutting the run conductor on certain types of connections, reduce cable cleaning requirements for old or reclaimed cable, and increase reliability under adverse field conditions.

Heavy duty connections are increasingly being specified for copper-coated steel conductor connections.

CERTIFICATIONS



DIAGRAMS



FEATURES

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

SPECIFICATIONS

Connects To: Identical Ground Rod

Table 1/1

Catalog Number	Ground Rod Type	Mold Family	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual	Certifications
HDGBR12	Steel	GB	3/8"	9.53 mm	cUL, UL
HDGBC14S	Steel	GB	1/2"	12.83 mm	UL, cUL
HDGBD31	Steel	GB	5/8"	15.88 mm	UL, cUL
HDGBD31W	Steel	GB	5/8"	15.88 mm	UL, cUL
HDGBF18	Copper-bonded	GB	3/4"	17.32 mm	cUL, UL
HDGBF18W	Copper-bonded	GB	3/4"	17.32 mm	UL, cUL
HDGED18	Copper-bonded	GE	3/4"	17.32 mm	
HDGBF33	Steel	GB	3/4"	19.05 mm	cUL, UL
HDGBF33W	Steel	GB	3/4"	19.05 mm	UL, cUL
HDGBF22	Copper-bonded	GB	1"	23.22 mm	UL, cUL
HDGBF37	Steel	GB	1"	25.4 mm	UL, cUL

ADDITIONAL PRODUCT DETAILS

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a TAC2Q2Q becomes XLTAC2Q2Q). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, 150 becomes XL150).

A gap between conductors may be required. See mold tag for more information.

HD-XX-X-XX-L-M-W		
HD	Heavy Duty Designation	
XX	Mold Family	
X	Price Key	
XX	Ground Rod Code	
L*	Split Crucible	Crucible section is split on molds designed with horizontal opening for easier cleaning
M*	Mold Only	
W*	Wear Plates	Reduce mechanical abrasion of molds at cable entry points

* Empty if none

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE