

Elbow 90-Degree Outside Top Opening Lay-in Hinged-Cover



Lay-in Hinged-Cover 90-Degree Elbow with Outside Top Opening are used for right-angle wireway installations. This elbow fitting allows a vertical drop to equipment below at a 90-degree corner while maintaining the top opening lay-in feature.

FEATURES

Lay-in Hinged-Cover 90-Degree Elbow with Outside Top Opening are used for right-angle wireway installations

This elbow fitting allows a vertical drop to equipment below at a 90-degree corner while maintaining the top opening lay-in feature

SPECIFICATIONS

- Color Code:** ANSI 61
- Finish:** Galvanized; Powder Coated
- Color:** Gray
- Material:** Mild Steel

Table 1/1						
Catalog Number	Type	Height	Width	Thickness	Sealing Plate Type	Sealing Plate Quantity
F88LE9AC	Elbow	203mm	203mm	1.9mm	Flat	2
F66LE9AC	Elbow	152mm	152mm	1.9mm	Flat	2
F44LE9AC	Elbow	102mm	102mm	1.9mm	Flat	2

ADDITIONAL PRODUCT DETAILS

Each sealing plate also includes one gasket and one set of screws to join sections.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE