

Heater

Compact heater without fan.



CERTIFICATIONS



FEATURES

Low surface temperature, protective insulation, and temperature limitation with PTC resistance

Assembly with clip-on attachment

Wide-range voltage input AC 120 ... 240 V

Compact heater without fan

SPECIFICATIONS

Table 1/1

Catalog Number	Power	Material	Package Quantity	Quick Ship
60715-220	10W	Plastic	1	No
60715-221	20W	Plastic	1	No
60715-222	50W	Plastic	1	No
60715-223	100W	Plastic	1	No

Catalog Number	Power	Material	Package Quantity	Quick Ship
60715-224	150W	Plastic	1	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE