

BC200-CD Conduit to Beam Clamp



CERTIFICATIONS



FEATURES

Eliminates offset bending conduit

Threaded hole on back

Ideal for electrical, mechanical, and HVAC applications

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel


Table 1/2

Catalog Number	Article Number	Outer Diameter (OD)	Flange Thickness (FT)	Rod Size (RS)	Torque (TQ)	Static Load
BC200CD2.5B	182240	31 - 38 mm	16 mm Max	6	4 N·m	440N
BC200CD2B	182230	25 - 33 mm	16 mm Max	6	4 N·m	440N
BC200CD1B	182220	19 - 25 mm	16 mm Max	6	4 N·m	440N

CatalogNumber	Article Number	Outer Diameter (OD)	Flange Thickness (FT)	Rod Size (RS)	Torque (TQ)	Static Load
BC200CD0B	182210	17 - 22 mm	16 mm Max	6	4 N·m	440N

Table 2/2		
Catalog Number	Article Number	Certifications
BC200CD2.5B	182240	UL, cUL
BC200CD2B	182230	cUL, UL
BC200CD1B	182220	cUL, UL, ITB
BC200CD0B	182210	UL, cUL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

