

# LHX+ Air/Liquid Heat Exchanger 115 V UL

## Data Solutions



### FEATURES

19" mountable Air/liquid heat exchanger with fan

Easy replaceable fans without dismounting the heat exchanger

Coolant feed from top or bottom

UL Certified

### SPECIFICATIONS

**Depth:** 500mm

**Product Type:** Air/Liquid Heat Exchanger

Table 1/2

| Catalog Number | Package Quantity | Supply Voltage | Redundant Power Supply | Coolant Feed | Height | Width |
|----------------|------------------|----------------|------------------------|--------------|--------|-------|
| 29714-022      | 1                | 115V min       | No                     | Bottom       | 266mm  | 426mm |
| 29714-036      | 1                | 115V min       | No                     | Bottom       | 266mm  | 426mm |
| 29714-033      | 1                | 115V min       | No                     | Bottom       | 266mm  | 426mm |
| 29714-027      | 1                | 115V min       | No                     | Bottom       | 266mm  | 426mm |

Table 2/2

| Catalog Number | Works With            |
|----------------|-----------------------|
| 29714-022      | Varistar, Varistar CP |
| 29714-036      | Varistar, Varistar CP |
| 29714-033      | Varistar, Varistar CP |
| 29714-027      | Varistar, Varistar CP |

## ADDITIONAL PRODUCT DETAILS

Please order separatly: Monitoring via Control unit, water control package, display and door contact switch.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**