

Rack-Mountable Tray 19-inch

Data Solutions



Fan trays enhance the natural convection airflow within a cabinet when installed with other 19-inch rack-mount equipment.

FEATURES

Fan trays available with either three or six 4-inch fans

Includes 72-inch (1829-mm) power cord with IEC 320 standard power socket

Power cord plugs into standard 115 VAC outlet

Lighted rocker switch provides on-off control and indicates when fans are on

SPECIFICATIONS

Color:	Jet Black
Material:	Mild Steel
Finish:	Powder Coated
Color Code:	RAL 9005

Table 1/2

Catalog Number	Article Number	Height	Width	Fan Quantity	Input Voltage AC	Depth
A19FT3B	13855	42mm	483mm	3	100 – 120V	206mm
A19FT6B	13856	42mm	483mm	6	100 – 120V	329mm

Table 2/2

Catalog Number	Article Number	Nominal Watts	Temperature	Thickness
A19FT3B	13855	45W	70°C max	1.52mm
A19FT6B	13856	90W	70°C max	1.52mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE