

Single-Sided Steel Vented Shelf

Data Solutions



The Single-Sided Steel Vented Shelf mounts to either front or rear flange of open-frame rack, supporting equipment that does not get mounted into rack angles. It uses 3U of rack space and is load rated for 150 lb. (68.0 kg).

FEATURES

The Single-Sided Steel Vented Shelf mounts to either front or rear flange of open-frame rack, supporting equipment that does not get mounted into rack angles

It uses 3U of rack space and is load rated for 150 lb. (68.0 kg)

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
ESH19V	35229	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
ESH23V	35239	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm

Table 2/2

Catalog Number	Article Number	Rack Units	Height	Width	Depth
ESH19V	35229	3U	123mm	482mm	267mm
ESH23V	35239	3U	123mm	584mm	267mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE