

CABS Module Kit, UL®



CERTIFICATIONS



FEATURES

Modules provide flexibility to select distance between phases and supports

Provides appropriate spacing between busbars in the same phase for cooling

Pins align with holes on support rails to allow for incremental positioning

Works with copper or aluminium busbar

Includes six insulators

Installs quickly and easily

Halogen free insulators

Compact design provides strength and rigidity

Engineered and standardized design

Time-savings and lower total install costs compared to traditional methods

RoHS compliant

SPECIFICATIONS

Typical Application Current Rating:	400 - 4500 A
Dielectric Strength, UL:	1000;1500
Material:	Glass Fibre Reinforced Polyamide

Flammability Rating:

UL® 94V-0

Working Temperature:

-40 to 130 °C


Catalog Number	CABS142T	CABS143T	CABS144T	CABS382T	CABS383T	CABS384T
Article Number	549500	549501	549502	549503	549504	549505
Busbars per Phase	1 - 2	1 - 3	1 - 4	1 - 2	1 - 3	1 - 4
Busbar Width	50.800 - 152.4 mm	50.800 - 152.4 mm	50.800 - 152.4 mm	50.800 - 152.4 mm	50.800 - 152.4 mm	50.800 - 152.4 mm
Busbar Thickness	6.35 mm	6.35 mm	6.35 mm	9.52 mm	9.52 mm	9.52 mm
Height (H)	54.6 mm	51.3 mm	48.3 mm	49.8 mm	49.8 mm	49.8 mm
Length (L)	57.2mm	76.2mm	95.3mm	76.2mm	95.2mm	114.3mm
Width (W)	81.3 mm	81.3 mm	81.3 mm	81.3 mm	81.3 mm	81.3 mm
Unit Weight	0.43 kg	0.7 kg	0.73 kg	0.56 kg	0.58 kg	0.86 kg
Certification Details	UL® 67 (CSA C22.2 No. 29) for Panelboards, 600 V Max UL® 891 (CSA C22.2 No. 244) for Switchboards, 600 V Max	UL® 67 (CSA C22.2 No. 29) for Panelboards, 600 V Max UL® 891 (CSA C22.2 No. 244) for Switchboards, 600 V Max	UL® 67 (CSA C22.2 No. 29) for Panelboards, 600 V Max UL® 891 (CSA C22.2 No. 244) for Switchboards, 600 V Max	UL® 67 (CSA C22.2 No. 29) for Panelboards, 600 V Max UL® 891 (CSA C22.2 No. 244) for Switchboards, 600 V Max	UL® 67 (CSA C22.2 No. 29) for Panelboards, 600 V Max UL® 891 (CSA C22.2 No. 244) for Switchboards, 600 V Max	UL® 67 (CSA C22.2 No. 29) for Panelboards, 600 V Max UL® 891 (CSA C22.2 No. 244) for Switchboards, 600 V Max

CatalogNumber	CABS142T	CABS143T	CABS144T	CABS382T	CABS383T	CABS384T
Complies With	IEC® 60439.1 IEC® 61439.1 IEC® 60695-2-11 (Glow Wire Test 960 °C) UL® 508A for Industrial Control Panels, 600 V Max UL® 508C for Power Conversion Equipment, 1000 V Max UL® 845 for Motor Control Centers, 600 V Max UL® 1558 for Low-Voltage Power Circuit Breaker Switchgear, 1000 V Max	IEC® 60439.1 IEC® 61439.1 IEC® 60695-2-11 (Glow Wire Test 960 °C) UL® 508A for Industrial Control Panels, 600 V Max UL® 508C for Power Conversion Equipment, 1000 V Max UL® 845 for Motor Control Centers, 600 V Max UL® 1558 for Low-Voltage Power Circuit Breaker Switchgear, 1000 V Max	IEC® 60439.1 IEC® 61439.1 IEC® 60695-2-11 (Glow Wire Test 960 °C) UL® 508A for Industrial Control Panels, 600 V Max UL® 508C for Power Conversion Equipment, 1000 V Max UL® 845 for Motor Control Centers, 600 V Max UL® 1558 for Low-Voltage Power Circuit Breaker Switchgear, 1000 V Max	IEC® 60439.1 IEC® 61439.1 IEC® 60695-2-11 (Glow Wire Test 960 °C) UL® 508A for Industrial Control Panels, 600 V Max UL® 508C for Power Conversion Equipment, 1000 V Max UL® 845 for Motor Control Centers, 600 V Max UL® 1558 for Low-Voltage Power Circuit Breaker Switchgear, 1000 V Max	IEC® 60439.1 IEC® 61439.1 IEC® 60695-2-11 (Glow Wire Test 960 °C) UL® 508A for Industrial Control Panels, 600 V Max UL® 508C for Power Conversion Equipment, 1000 V Max UL® 845 for Motor Control Centers, 600 V Max UL® 1558 for Low-Voltage Power Circuit Breaker Switchgear, 1000 V Max	IEC® 60439.1 IEC® 61439.1 IEC® 60695-2-11 (Glow Wire Test 960 °C) UL® 508A for Industrial Control Panels, 600 V Max UL® 508C for Power Conversion Equipment, 1000 V Max UL® 845 for Motor Control Centers, 600 V Max UL® 1558 for Low-Voltage Power Circuit Breaker Switchgear, 1000 V Max

ADDITIONAL PRODUCT DETAILS

Typical Application Rating is dependent upon busbar size, current rating, temperature, and enclosure size.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE