

## APO Cover



APO Covers are designed for use as inspection windows in highly corrosive environments where easy viewing and access is essential.

### FEATURES

---

Covers are maintenance free and corrosion resistant

Included thumb screw inserts allow quick window opening for access to interior component

## SPECIFICATIONS

**Material:** Fiberglass  
**Color:** Light Gray  
**Color Code:** RAL 7035  
**Finish:** Smooth Matte

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Quick Ship |
|----------------|----------------|--------|-------|-------|------------|
| A1-COVERLG     | A1-COVERLG     | 186mm  | 151mm | 45mm  | No         |
| A1-CTCOVER     | A1-CTCOVER     | 186mm  | 151mm | 45mm  | No         |
| A31-COVERLG    | A31-COVERLG    | 302mm  | 186mm | 45mm  | No         |
| A31-CTCOVER    | A31-CTCOVER    | 302mm  | 186mm | 45mm  | No         |
| A41-COVERLG    | A41-COVERLG    | 302mm  | 302mm | 45mm  | No         |
| A41-CTCOVER    | A41-CTCOVER    | 302mm  | 302mm | 45mm  | No         |
| A51-COVERLG    | A51-COVERLG    | 488mm  | 302mm | 45mm  | No         |
| A51-CTCOVER    | A51-CTCOVER    | 488mm  | 302mm | 45mm  | No         |
| A71-COVERLG    | A71-COVERLG    | 372mm  | 302mm | 45mm  | No         |
| A71-CTCOVER    | A71-CTCOVER    | 372mm  | 302mm | 45mm  | No         |
| A11-COVERLG    | A11-COVERLG    | 603mm  | 372mm | 45mm  | No         |
| A11-CTCOVER    | A11-CTCOVER    | 603mm  | 372mm | 45mm  | No         |
| A12-COVERLG    | A12-COVERLG    | 603mm  | 603mm | 45mm  | No         |
| A12-CTCOVER    | A12-CTCOVER    | 603mm  | 603mm | 45mm  | No         |
| A61-COVERLG    | A61-COVERLG    | 603mm  | 302mm | 45mm  | No         |
| A61-CTCOVER    | A61-CTCOVER    | 603mm  | 302mm | 45mm  | No         |

| Catalog Number | Article Number | Height | Width | Depth | Quick Ship |
|----------------|----------------|--------|-------|-------|------------|
| A81-COVERLG    | A81-COVERLG    | 558mm  | 302mm | 45mm  | No         |
| A81-CTCOVER    | A81-CTCOVER    | 558mm  | 302mm | 45mm  | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE