

# Dual-Access Safety Lockout



Dual-Access Safety Lockouts provide a means of using two padlocks on a secured power source. Either padlock can be removed enabling power to be interrupted and enclosure accessed. Padlock holes are .38-in. (10-mm) in diameter.

## FEATURES

---

Padlock is not included

Catalog number ASLDAC includes a 10.00-in. (254-mm) plated steel chain

SPECIFICATIONS

| Table 1/1      |                |            |               |            |            |           |
|----------------|----------------|------------|---------------|------------|------------|-----------|
| Catalog Number | Article Number | Material   | Finish        | Color      | Color Code | Thickness |
| ASLDAC         | 11390          | Mild Steel | Powder Coated | Signal Red | RAL 3001   | 3.4mm     |
| ASLDA          | 11380          | Mild Steel | Powder Coated | Signal Red | RAL 3001   | 3.4mm     |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE