

ProLine-PC Door for Lower Front



Solid door with foam-in-place gasket. Hidden hinges provide 140-degree swing from either left or right side (180-degree hinge is available). Doors have a Small Flush Bezel with tool-to-open insert. Other inserts and a Flush Swing Handle also are available.

FEATURES

Side hinged doors with 140-degree swing

Seamless foam in place gasket

SPECIFICATIONS

Thickness: 1.52mm

Table 1/1						
Catalog Number	Article Number	Material	Color	Color Code	Finish	Quick Ship
PDS88	98680	Mild Steel	Light Gray	RAL 7035	Powder Coated	No
PDS86	98670	Mild Steel	Light Gray	RAL 7035	Powder Coated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE