


RackChiller CDU40 Coolant Distribution Unit



The nVent HOFFMAN RackChiller CDU40 is a rack-based Coolant Distribution Unit (CDU), built for the needs of today's most demanding HPC requirements. Capable of managing 40kW+ of heat load in a remarkably small 4U of space. The RackChiller CDU40 is an extremely efficient heat exchanger that uses ASHRAE W4 warm water to manage processor and component heat.

INDUSTRY STANDARDS

UR/cUR Recognized

CE

FEATURES

Manages 40kW+ of processor load per network

Compatible with ASHRAE W4 warm water cooling

N+1 redundant centralized pumps

Dry-break quick disconnects (optional)

5-inch LCD screen with touch functionality

Integrated control and monitoring system (Webserver, Modbus, SNMP)

Internal and external leak detection system

4U rack-mount chassis

Warm water cooling reduces the need for chillers



Quick and easy installation and service

Pump redundancy: 3 pumps for n+1 redundancy

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height (H)	Width (W)	Depth (D)	Material	Finish
CDU0402R001	57118	177mm	430mm	994mm	Mild Steel	Plated
CDU0402R001Q	57117	177mm	430mm	994mm	Mild Steel	Plated

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE