

Syspend 281-MAX Adjustable Feet



Syspend 281-MAX Adjustable Feet will screw to the bottom of the Flex Base to help balance and keep stable.

FEATURES

Adjustable Overall Height: 35-45mm

Load capacity per adjustable feet: 110 lbs (50 kg)

Four pieces per set

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Depth	Material	Finish
S2MFBF	59362	60mm	40mm	40mm	Aluminum	Mill

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE