

RackPower PDU, RP1xxx, 120/208 VAC, 3-phase

Power Utilities

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design with only 44 mm height.

FEATURES

RackPower RP1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input Voltage Range 100-120/200-240VAC, 3-phase WYE

Connecting cable 6", with NEMA L21 connector

C13 and C13/C19 Combo outlets

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Color	Length	Voltage AC	Function
RP1851	Socket Strip	IEC C13, IEC C13/C19	Black	1780 mm	208 V	Input Monitored

Table 2/2

Catalog Number	Depth	Width
RP1851	55 mm	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE