

# Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame

## Power Utilities

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

### FEATURES

Open at front (no door)

19" panel mounts integrated into decoration frame

Rear door with single point locking, side panels with quick release fastener

Static load-carrying capacity 400 kg (mounted at decoration frame)

### SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Height | Height  | Frame Color | Width  | Frame Color Code | Cladding Material |
|----------------|-------------|---------|-------------|--------|------------------|-------------------|
| 10630-034      | 38 U        | 1800 mm | Black Grey  | 600 mm | RAL 7021         | Steel             |
| 10630-033      | 38 U        | 1800 mm | Black Grey  | 600 mm | RAL 7021         | Steel             |
| 10630-035      | 42 U        | 2000 mm | Black Grey  | 600 mm | RAL 7021         | Steel             |
| 10630-036      | 42 U        | 2000 mm | Black Grey  | 600 mm | RAL 7021         | Steel             |

Table 2/3

| Catalog Number | Depth | Cladding Color | Cladding Color Code | Complies With | Frame Material | Product Type |
|----------------|-------|----------------|---------------------|---------------|----------------|--------------|
|----------------|-------|----------------|---------------------|---------------|----------------|--------------|

|           |        |            |          |                 |       |         |
|-----------|--------|------------|----------|-----------------|-------|---------|
| 10630-034 | 800 mm | Black Grey | RAL 7021 | IEC 60297-3-100 | Steel | Cabinet |
| 10630-033 | 600 mm | Black Grey | RAL 7021 | IEC 60297-3-100 | Steel | Cabinet |
| 10630-035 | 600 mm | Black Grey | RAL 7021 | IEC 60297-3-100 | Steel | Cabinet |
| 10630-036 | 800 mm | Black Grey | RAL 7021 | IEC 60297-3-100 | Steel | Cabinet |

Table 3/3

| Catalog Number | Static Load |
|----------------|-------------|
| 10630-034      | 400 kgf     |
| 10630-033      | 400 kgf     |
| 10630-035      | 400 kgf     |
| 10630-036      | 400 kgf     |

## ADDITIONAL PRODUCT DETAILS

Lever handle can be added to rear door.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**