

# **300M Universal Beam Clamp**



## **CERTIFICATIONS**







## **FEATURES**

Universal beam clamp for standard beams

Structural attachment (with infinite adjustment) to top or bottom flange of metal beams to support hanger rod

Including set screw and lock nut

## **SPECIFICATIONS**

Material: Cast Iron

Finish: Electrogalvanized

Table 1/2							
Catalog Number	Article Number	Hole Type	Hole Size (HS)	Thread Size (TS)	Flange Thickness (FT)	A	
30009MM	389500	Plain	9 mm		18 mm Max	21 mm	
30011MM	389510	Plain	11 mm		20 mm Max	23 mm	
30013MM	389520	Plain	13 mm		26 mm Max	35 mm	


CatalogNumber	Article Number	Hole Type	Hole Size (HS)	Thread Size (TS)	Flange Thickness (FT)	A
30017MM	389505	Plain	17 mm		28 mm Max	30 mm
300M10	386820	Threaded		M10	20 mm Max	23 mm
300M12	386830	Threaded		M12	26 mm Max	35 mm


Table 2/2						
<b>Catalog Number</b>	Article Number	Torque (TQ)	Static Load	Certifications		
30009MM	389500	14 N·m Min	1200N	VdS G4005005, ITB		
30011MM	389510	14 N·m Min	2500N	VdS G4005005, FM Approved, Pipe Hanger Components, ITB		
30013MM	389520	14 N·m Min	3500N	FM Approved, Pipe Hanger Components, VdS G4913044, ITB		
30017MM	389505	14 N·m Min	5500N	ITB, FM Approved, Pipe Hanger Components, VdS G4031026		
300M10	386820	14 N·m Min	2500N	ITB, VdS G4005005, FM Approved, Pipe Hanger Components		
300M12	386830	14 N·m Min	3500N	FM Approved, Pipe Hanger Components, VdS G4913044, ITB		

# **ADDITIONAL PRODUCT DETAILS**

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

# **DIAGRAMS**





#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

## Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

