We connect and protect

Telecom Main Grounding Busbar, 394 mm

Data Solutions

CATALOG NUMBER

TMGBA16L19P



CERTIFICATIONS

FEATURES

- Meets TIA-607-C and TIA-607-D and conforms to BICSI® recommendations
- Complies with NEMA® standards
- Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)
- Telecom grounding busbar splice kits are available to extend the length of the busbar

PRODUCT ATTRIBUTES

- Material: Copper
- Tin Plating: No
- Width (W): 101.6mm
- Thickness (T): 6.35mm
- Length 1 (L1): 394mm

Length 2 (L2): 229mm
Hole Size 1 (HS1): 0.3125in
Hole Size 1 Number of Pairs: 19
Hole Size 2 (HS2): 0.4375in
Hole Size 2 Number of Pairs: 3
A: 25.4mm
B: 28.6mm
C: 15.9mm
D: 15.9mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.