

ESE Air Terminal for Remote Tester



The nVent ERICO Early Streamer Emission (ESE) Air Terminal for Remote Tester generates controlled magnitude and frequency pulses at the tip of the terminal during high static fields before a lightning discharge. Due to the internal control circuit, the nVent ERICO ESE Air Terminal for Remote Tester enables early launching of an upward leader compared to other passive components. When paired with the nVent ERICO ESE Air Terminal Remote Tester, the need for on-site manual testing is eliminated and creates a more autonomous, continuous monitoring solution.

FEATURES

Designed and tested to NF C 17-102 and similar standards

Superior corrosion resistance, even in high salinity environments

Quick and easy installation

Compatible with nVent ERICO ESE Air Terminal Remote Tester

Suitable for use with a variety of downconductor systems including tape and stranded conductors in addition to insulated downconductors such as nVent ERICO ISONV and nVent ERICO Ericore conductors

SPECIFICATIONS


Table 1/2

Catalog Number	Complies With	Connects To	Triggered Advance, ΔT	Temperature	Diameter ($\varnothing$)	Height (H)
SI60I316RT	NF C17-102:2011, NP 4426:2013, UNE 21186:2011	ESEAT Remote Tester (SIREMOTETES TER)	60 μ s	120 °C Max	28 mm	684.6 mm

Table 2/2

Catalog Number	Material	Thread Size (TS)	Unit Weight
SI60I316RT	Stainless Steel 316L (EN 1.4404)	MF25	1.56 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE