

Telecom Grounding Busbar



CERTIFICATIONS



FEATURES

Meets TIA-607-C and TIA-607-D conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

SPECIFICATIONS

Thickness (T): 6.35 mm

Width (W): 50.8 mm

Material: Copper

Table 1/2


Catalog Number	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 (HS1)	Hole Size 1 Number of Pairs	Hole Size 2 (HS2)
TGBA20L12PT	Yes	508 mm	229 mm	8 mm	12	11 mm

CatalogNumber	Tin Plating	Length 1 (L1)	Length 2 (L2)	Hole Size 1 (HS1)	Hole Size 1 Number ofPairs	Hole Size 2 (HS2)
TGBA18L10P	No	451 mm	229 mm	8 mm	10	11 mm
TGBA29L18PT	Yes	737 mm	457 mm	8 mm	18	11 mm
TGBA24L14PT	Yes	610 mm	457 mm	8 mm	14	11 mm
TGBA18L10PT	Yes	451 mm	229 mm	8 mm	10	11 mm
TGBA24L14P	No	610 mm	457 mm	8 mm	14	11 mm
TGBA16L08PT	Yes	394 mm	229 mm	8 mm	8	11 mm
TGBA12L06PT	Yes	305 mm	229 mm	8 mm	6	11 mm
TGBA20L12P	No	508 mm	229 mm	8 mm	12	11 mm
TGBA29L18P	No	737 mm	457 mm	8 mm	18	11 mm
TGBA12L06P	No	305 mm	229 mm	8 mm	6	11 mm
TGBA16L08P	No	394 mm	229 mm	8 mm	8	11 mm

Table 2/2				
Catalog Number	Hole Size 2 Number of Pairs	A	B	C
TGBA20L12PT	3	25.4 mm	28.6 mm	15.9 mm
TGBA18L10P	3	25.4 mm	28.6 mm	15.9 mm
TGBA29L18PT	5	25.4 mm	28.6 mm	15.9 mm
TGBA24L14PT	5	25.4 mm	28.6 mm	15.9 mm
TGBA18L10PT	3	25.4 mm	28.6 mm	15.9 mm

Catalog Number	Hole Size 2 Number of Pairs	A	B	C
TGBA24L14P	5	25.4 mm	28.6 mm	15.9 mm
TGBA16L08PT	3	25.4 mm	28.6 mm	15.9 mm
TGBA12L06PT	3	25.4 mm	28.6 mm	15.9 mm
TGBA20L12P	3	25.4 mm	28.6 mm	15.9 mm
TGBA29L18P	5	25.4 mm	28.6 mm	15.9 mm
TGBA12L06P	3	25.4 mm	28.6 mm	15.9 mm
TGBA16L08P	3	25.4 mm	28.6 mm	15.9 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE