

FS66S Side-Mounted Subpanel



The panel is mounted to interior left or right side of an enclosure to accommodate components for type FM FS66S. One piece for each.

FEATURES

Includes all necessary mounting hardware.

SPECIFICATIONS

Material: Mild Steel
Finish: Powder Coated
Color: White

Table 1/1

Catalog Number	Thickness	Fits Enclosure Height	Fits Enclosure Depth	Quick Ship
FMMP1504G020S	2.5mm	1500mm	59.1mm	No
FMMP1505G020S	2.5mm	1500mm	59.1mm	No
FMMP1805G020S	2.5mm	1800mm	70.9mm	No
FMMP1806G020S	2.5mm	1800mm	70.9mm	No
FMMP2005G020S	2.5mm	2000mm	78.7mm	No
FMMP2006G020S	2.5mm	2000mm	78.7mm	No
FMMP2106G020S	2.5mm	2100mm	82.7mm	No
FMMP2108G020S	2.5mm	2100mm	82.7mm	No
FMMP2205G020S	2.5mm	2200mm	86.6mm	No
FMMP2206G020S	2.5mm	2200mm	86.6mm	No
FMMP2208G020S	2.5mm	2200mm	86.6mm	No
FMMP2310G020S	2.5mm	2300mm	90.6mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE