

MOD0 Swing Panel Partial



Affixed to the enclosure with hinges and latches, horizontally adjustable, adapted to install components that have to be frequently checked, such as instruments.

FEATURES

Partial panel (500mm high), horizontally adjustable

100kg maximum load

Opened in the same direction as front door

One per package, mounting hardware included

SPECIFICATIONS

Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1				
Catalog Number	Thickness	Fits Enclosure Height	Fits Enclosure Width	Quick Ship
MDSF0508C540S	1.5mm	500mm	800mm	No
MDSF0508C541S	1.5mm	500mm	800mm	No
MDSF0509C540S	1.5mm	500mm	900mm	No
MDSF0509C541S	1.5mm	500mm	900mm	No
MDSF0510C540S	1.5mm	500mm	1000mm	No
MDSF0510C541S	1.5mm	500mm	1000mm	No
MDSF0512C540S	1.5mm	500mm	1200mm	No
MDSF0512C541S	1.5mm	500mm	1200mm	No
MDSF0513C540S	1.5mm	500mm	1300mm	No
MDSF0513C541S	1.5mm	500mm	1300mm	No
MDSF0516C540S	1.5mm	500mm	1600mm	No
MDSF0516C541S	1.5mm	500mm	1600mm	No
MDSF0518C540S	1.5mm	500mm	1800mm	No
MDSF0518C541S	1.5mm	500mm	1800mm	No
MDSF0524C540S	1.5mm	500mm	2400mm	No
MDSF0524C541S	1.5mm	500mm	2400mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE