

# Interscale for Embedded NUC, Conduction Cooled, 34 mm, 112, mm 107 mm

## CATALOG NUMBER

**14820-701**



Small form factor case with integrated EMC-shielding and conduction cooling for eNUC boards, based on the innovative and flexible nVent SCHROFF Interscale platform.

## CERTIFICATIONS



## FEATURES

Modular case consisting of 3 easy to assemble parts; body, topcover and front panel

Integrated EMC protection

Compliant with the SDT.03 embeddedNUC standard <http://www.sget.org/standards.html>

Cutouts specific for IES MB95 embeddedNUC board (<http://en.ies.de/>)

Rigid construction requires only two screws

Perforated side panels for passive cooling

Board mounting studs installed

Color RAL 7016

Other dimensions, cutout shapes or locations and screenprinting available

## PRODUCT ATTRIBUTES

Product Type: Small Form Factor Case

Product Family: Interscale

Type: Desktop

Height: 34mm

Width: 112mm

Depth: 106.5mm

Material: Aluminum

Color: Anthracite Grey

Color Code: RAL 7016

Finish: Powder Coated

Protection Rating: IP20

Cooling: Perforated

Package Quantity: 1

Net Weight: 0.175kg

## ADDITIONAL PRODUCT DETAILS

Modified or customized cases upon request.

Only the listed Interscale accessories are compatible.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**