

LED Lights for Cabinets



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

CERTIFICATIONS



FEATURES

Lights can be easily mounted vertically or horizontally.

Simple through-wiring based on a plug-and-play system.

SPECIFICATIONS

Product Type: Light

Table 1/4

Catalog Number	Input Voltage AC	Accessory Type	Input Voltage DC	Length	Package Quantity	Color
57274	250V max	Lights			1	Black
57275		Lights			2	Black
57265	230V max	Lights	24V max	396mm	1	Black
57272	250V max	Lights		3000mm	1	Black

CatalogNumber	Input Voltage AC	AccessoryType	Input Voltage DC	Length	Package Quantity	Color
57273	250V max	Lights		1000mm	1	Black

Table 2/4

Catalog Number	Depth	Finish	Height	Material	Protection Rating	Type
57274	14mm	Smooth Matte	53mm	Plastic	IP20	Cabinet Light, Terminal Block
57275	4mm	Smooth Matte	30mm		IP20	Cabinet Light, Magnet
57265	40mm	Smooth Matte		Plastic	IP20	Cabinet Light
57272		Smooth Matte		Plastic	IP20	Connection Cable
57273		Smooth Matte		Plastic	IP20	Cabinet Light

Table 3/4

Catalog Number	Width	Color Temperature	Nominal Voltage	Operating Temperature	Weight	Certifications
57274	18mm		250V	60°C min	0.07kg	RoHS
57275	12mm				0.08kg	RoHS
57265	33mm	5800K	230V	-20 to 55°C	0.24kg	CE, RoHS
57272	0.3mm		250V	60°C min	0.3kg	RoHS
57273			250V	60°C min	0.3kg	RoHS

Table 4/4

Catalog Number	Quick Ship
57274	No
57275	No

Catalog Number	Quick Ship
57265	No
57272	No
57273	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE