

# nVent CADDY Speed Link SLK with Wedge Anchor



## **FEATURES**

Complete system includes wire, locking device and wedge anchor from fischerwerke GmbH &Co. KG

Quickly and easily attaches into cracked and non-cracked concrete

No special tools required

ETA 06/0175 approval available from fischerwerke GmbH &Co. KG

# **SPECIFICATIONS**

Wire Rope Diameter: 2 mm

Static Load Safety Factor: 5:1

Drill Bit Diameter: 6mm

Drill Hole Depth: 31mm

Finish: Electrogalvanized

Material: Steel;Polypropylene;Zinc Alloy


**Embedment Depth:** 25 mm Min

Table 1/2							
Catalog Number	Article Number	Wire Rope Length	Length (L)	Height (H)	Width (W)	Thickness (T)	
SLK2L5WA6	196736	5m	63.5mm	55 mm	19 mm	12.5 mm	
SLK2L2WA6	196734	2m	54mm	55 mm	19 mm	12.5 mm	

CatalogNumber	Article Number	Wire Rope Length	Length (L)	Height (H)	Width (W)	Thickness (T)
SLK2L3WA6	196735	3m	54mm	55 mm	19 mm	12.5 mm

Table 2/2							
Catalog Number	Article Number	Angle (a)	Static Load				
SLK2L5WA6	196736	90 ° Max	440N				
SLK2L2WA6	196734	90 ° Max	300N				
SLK2L3WA6	196735	90 ° Max	300N				

# **DIAGRAMS**



# WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

## **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

## **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

