

SK Single Piece Strut Clamp for Conduit



CERTIFICATIONS





FEATURES

One piece break apart strut clamp for EMT and Rigid conduit

Includes thread impression and captured screw

SPECIFICATIONS


Finish: Electrogalvanized


Material: Steel

Table 1/1						
Catalog Number	Article Number	Outer Diameter (OD)	Width (W)	Static Load		
SK85I	190090	17.9 - 21.3 mm	32 mm	890N		
SK125I	190000	23.4 - 26.7 mm	32 mm	890N		
SK165I	190010	29.5 - 33.4 mm	32 mm	890N		

Catalog Number	Article Number	Outer Diameter (OD)	Width (W)	Static Load
SK205I	190020	38.4 - 42.2 mm	32 mm	890N
SK645I	190080	114.3 mm	32 mm	1560N
SK245I	190030	44.2 - 48.3 mm	32 mm	890N
SK325I	190040	55.8 - 60.3 mm	32 mm	890N
SK405I	190050	73 mm	32 mm	1560N
SK485I	190060	88.9 mm	32 mm	1560N

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

