

Telecom Main Grounding Busbar, 305 mm

Data Solutions

CATALOG NUMBER

TMGBA12L15P



CERTIFICATIONS



FEATURES

Meets TIA-607-C and TIA-607-D and conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

PRODUCT ATTRIBUTES

Material: Copper

Tin Plating: No

Width (W): 101.6mm

Thickness (T): 6.35mm

Length 1 (L1): 305mm

Length 2 (L2): 229mm

Hole Size 1 (HS1): 0.3125in

Hole Size 1 Number of Pairs: 15

Hole Size 2 (HS2): 0.4375in

Hole Size 2 Number of Pairs: 3


A: 25.4mm

B: 28.6mm

C: 15.9mm

D: 15.9mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE