

# Slide

## Data Solutions



Heavy-duty ball bearing, plated three-section Slides are 16-in. (406-mm) long and allow 17-in. (423-mm) extension. They are attached to supports that mount between two pairs of rack mounting angles that have accessory mounting legs. Mounting hardware is furnished. Equipment 16.75-in. (425-mm) wide can be mounted between Slide assemblies installed on 19-in. rack angles. A pair of Slides can support up to 160 lbs. at the extended position when load is distributed evenly along the 16-in. (406-mm) Slide length. Requires Rack Angle Adapter Bracket to fit ProLine.

### FEATURES

Heavy-duty ball bearing slides are 16-in. (406-mm) long and allow 17-in. (423-mm) extension

Slides attach to supports that mount between two pairs of rack mounting angles that have accessory mounting legs

A pair of Slides can support up to 160 lbs. (72 kg) at the extended position when load is distributed evenly

Mounting hardware is furnished

### SPECIFICATIONS

Table 1/1

Catalog Number	Material	Finish
IA16SL2U0000S	Mild Steel	Zinc Plated

### ADDITIONAL PRODUCT DETAILS

Needs to be used with the Rack Angle Adapter Bracket (PBRAA, PBRAA19 or PBRAA24).

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**