

nVent ERICO Cadweld Plus Impulse Exothermic Welding Control Unit, 4.5 m Cable

CATALOG NUMBER

PLUSCU2L15



Our latest innovation, the nVent ERICO Cadweld Plus Impulse Exothermic Welding Control Unit, brings you the highest level of flexibility and ease of use of any of our ignition systems. Precision engineered, the control unit lets you choose your power source: from off-the-shelf AA-batteries to the rechargeable Lithium-Ion packs you have on your job site.

Why should you choose our latest ignition system? Safety, Power and Ease-of-Use.

CERTIFICATIONS



FEATURES

Enhanced power tool style grip is ergonomic and easy to hold

Self-closing trigger guard prevents accidental ignition, providing added safety

LED ignition counter provides instant feedback on the timing of the ignition and is visible in sunny outdoor conditions

Five second delay in ignition is a safety feature to allow the user to stop ignition, if necessary

Battery life indicator integrated into the unit for real-time updates on battery life; compatible with both AA and rechargeable batteries

Includes AA alkaline batteries to power approximately 600 connections

Rechargeable batteries from Milwaukee® or DEWALT® can be used to power approximately 1500 connections using a 4Ah battery

Battery adapters available for use with either Milwaukee® or DEWALT® rechargeable batteries (sold separately)

High temperature lead with single molded insert into the unit keeps the most-often replaced component of ignition systems more securely attached and reliable

Easy-to-use alligator clip design of the termination clearly shows a positive connection in the viewing window

PRODUCT ATTRIBUTES

Cable Length: 4.6m

Battery Information: 8 Standard AA Batteries

Working Temperature: -18 to 54 °C

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE