

# Rail Crown Socket



#### **FEATURES**

Cast bronze mechanical electrical connection to rail

Crown socket is tin plated to improve rail interface electrical properties

Primarily for traction power negative return current

Secured to the rail with a threaded tapered pin

Attaches to cable simply and permanently using the nVent ERICO Cadweld connection process

Suitable for cables up to and including 500 kcmil/240 mm<sup>2</sup>

Available for field-made applications or as part of a factory-made assembly

No special tools required

#### **SPECIFICATIONS**

Table 1/1		
Catalog Number	Product	Conductor Size
B1883QA	Socket	500 kcmil Stranded, 240 mm² Stranded
B1883QB	Pin	
B1883QC	Pin, Oversized	

### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

# North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE