

# MFSHT-2 nVent ERIFLEX Flexibar Manual Shearing Tool



## CERTIFICATIONS



## FEATURES

Cuts nVent ERIFLEX Flexibar quickly and accurately without burrs or deformation

Cuts through the insulation without damaging it

Maximum nVent ERIFLEX Flexibar shearing 5x32x1

Adjustable abutment for identical and repetitive cuttings

Abutment and indicator allow for easy cutting of 45° chamfers

Elastomer edge near the blade helps to prevent jamming from shavings

Replacement blade available

RoHS compliant

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material           | Conductor Thickness | Conductor Width | Depth | Height |
|----------------|----------------|--------------------|---------------------|-----------------|-------|--------|
| MFSHT-2        | 559146         | Steel,<br>Aluminum | 5 mm                | 32 mm Max       | 200mm | 750 mm |

| Table 2/2      |                |        |             |
|----------------|----------------|--------|-------------|
| Catalog Number | Article Number | Width  | Unit Weight |
| MFSHT-2        | 559146         | 160 mm | 6 kg        |

ADDITIONAL PRODUCT DETAILS

Tool must be installed on a table.

Do not use to cut solid busbar.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE