

# Elbow 90-Degree Feed-Through



Feed-Through 90-Degree Elbows are used for continuous runs with 90-degree turns. Connects to other wireway sections and fittings and protects wires and cables against dust in a broad range of industrial applications.

## INDUSTRY STANDARDS

---

Certified by Canadian Standards Association.

## FEATURES

---

Feed-Through 90-Degree Elbows are used for continuous runs with 90-degree turns

Connects to other wireway sections and fittings and protects wires and cables against dust in a broad range of industrial applications

## SPECIFICATIONS

**Color Code:** ANSI 61  
**Color:** Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated

Table 1/1

| Catalog Number | Article Number | Type  | Height | Width | Thickness | Quick Ship |
|----------------|----------------|-------|--------|-------|-----------|------------|
| F88WE90        | 14680          | Elbow | 203mm  | 203mm | 1.9mm     | No         |
| F66WE90        | 14470          | Elbow | 152mm  | 152mm | 1.9mm     | No         |
| F44WE90        | 14260          | Elbow | 102mm  | 102mm | 1.9mm     | No         |
| F22WE90        | 14070          | Elbow | 64mm   | 64mm  | 1.9mm     | No         |

## ADDITIONAL PRODUCT DETAILS

All dimensions are to outside surfaces. Allow .12 in. (3 mm) additional for gasket at joints. Dimension K is from intersection of center lines.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**