

## Filler Plates, MPF



These filler plates provide a flat mounting surface in bayed enclosures when the mounting plate is not fitted flush with the frame. The continuous mounting surface created allows the space to be used more efficiently.

### FEATURES

---

Description: Covers the space between pairs of adjacent mounting plates to provide a continuous working surface, when two enclosures are mounted together.

Material: 2 mm zinc plated steel.

Pack quantity: 1 plate with mounting accessories.

SPECIFICATIONS

Thickness: 2mm  
Material: Mild Steel  
Finish: Zinc Plated

| Table 1/1      |                |        |       |       |                    |            |
|----------------|----------------|--------|-------|-------|--------------------|------------|
| Catalog Number | Article Number | Height | Width | Depth | Enclosure Material | Quick Ship |
| MPF1800        | MPF1800        | 1800mm | 102mm | 25mm  | Mild Steel         | No         |
| MPF2200        | MPF2200        | 2200mm | 102mm | 25mm  | Mild Steel         | No         |
| MPF2000        | MPF2000        | 2000mm | 102mm | 25mm  | Mild Steel         | No         |

ADDITIONAL PRODUCT DETAILS

For bayed configurations MPD02 must be used along with the fixation brackets supplied with the enclosure and mounting plate. MPA06 must be used if the enclosure comes without fixation brackets. MPF cannot be used with mounting plates if they are installed in the most rear position.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE