

Vertical Pouring Basin, Standard



Standard vertical pouring basins should be used whenever the clearances of the structure allow. The compact size of the standard pouring basins help ensure the best possible flow of filler material.

FEATURES

Made from heat-resistant graphite

Durable, re-usable and long lasting

Designed for use with T-Series and B-Series vertical sleeves

SPECIFICATIONS

Material: Graphite

Table 1/1

Catalog Number	Diameter (Ø)	Length 1 (L1)	Length 2 (L2)	Width (W)	Height 1 (H1)	Height 2 (H2)
RBWS1500U	35 mm	137 mm	38 mm	76 mm	124mm	70mm
RBWS1500X	38 mm	137 mm	38 mm	76 mm	124mm	70mm
RBWS1481F	64 mm	152 mm	38 mm	76 mm	159mm	95mm
RBWS1481G	70 mm	152 mm	38 mm	76 mm	159mm	95mm
RBWS1481H	7					

CatalogNumber	Diameter (Ø)	Length 1 (L1)	Length 2 (L2)	Width (W)	Height 1 (H1)	Height 2 (H2)
RBWS1481K	86 mm	152 mm	38 mm	76 mm	159mm	95mm
RBWS1482K	86 mm	165 mm	38 mm	76 mm	191mm	108mm
RBWS1482M	95 mm	165 mm	38 mm	76 mm	191mm	108mm
RBWS1499D	54 mm	149 mm	38 mm	76 mm	140mm	76mm
RBWS1499F	64 mm	149 mm	38 mm	76 mm	140mm	76mm
RBWS1499G	70 mm	149 mm	38 mm	76 mm	140mm	76mm
RBWS1499H	73 mm	149 mm	38 mm	76 mm	140mm	76mm
RBWS1500A	41 mm	137 mm	38 mm	76 mm	124mm	70mm
RBWS1500C	48 mm	137 mm	38 mm	76 mm	124mm	70mm
RBWS1500D	54 mm	137 mm	38 mm	76 mm	124mm	70mm
RBWS1500E	57 mm	137 mm	38 mm	76 mm	124mm	70mm
RBWS1500F	64 mm	137 mm	38 mm	76 mm	124mm	70mm

ADDITIONAL PRODUCT DETAILS

RBWS1481, RBWS1482, RBWS1499 and RBWS1500 pouring basins require one RBM2660 pouring basin frame (sold separately).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

