

nVent CADDY Cable/Conduit Stud Attachment, Multifunction




The nVent CADDY Cable/Conduit Stud Attachment, Multifunction is a simplified, easy-to-use solution for mounting both EMT and flexible conduit above electrical boxes. Its universal design eliminates the need to carry multiple parts on the job and allows contractors to utilize just one fastener. Additionally, the Cable/Conduit Stud Attachment, Multifunction increases functionality by featuring a wider bracket to span across the entirety of the electrical box and reach all three knockouts. Whether you're securing EMT, flexible conduit or both, rest assured, this simple solution improves productivity while keeping your job site safe.

FEATURES

- Multifunction design allows for different securement combinations such as one EMT and up to two flexible conduit cables or three conduit cables
- Capable of securing EMT sizes spanning from ½ to 1 in
- Score marks to break off excess bracket
- Compliant with NEC® Article 358.30(A), which requires conduit support within 36" of an electrical box
- Compliant with CEC Rule 12-1404, which requires conduit support within 1 m of an electrical box
- Compliant with CEC Rule 12-618, which requires support of armored cable within 300 mm (12") of an electrical box

Material: Steel Finish: nVent CADDY Armour

Catalog Number	EMT Conduit Size	MC/AC Cable Size	Outer Diameter 1 OD1	Outer Diameter 2 OD2	Outer Diameter OD	Box Depth
CS816M	0.5" - 1"	14-2 to 2-3	1/2" Max	1/2" Max	1/2 - 1"	2.125"



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

