

# 920 Series, Solid-State Relay



RAYCHEM 920 Series - SSR provides electronic switching capability for heat trace circuits. Available in 1-,2-, or 3-pole solid-state, normally open relay , 277V or 600V, and 30A or 60A at 104°F (40°C). Allows for proportional, power limiting, and soft start control algorithms.

## FEATURES

Easy to install

Suitable for Class I Div. 2/Zone 2 hazardous locations

Infinite Life Cycle

## SPECIFICATIONS

Table 1/1

Catalog Number	Item Name	Voltage Rating	Current Rating
10260-008	SS3	277 V max	30 A
10260-009	SSH3	600 V max	30 A
10260-011	SSH6	600 V max	60 A

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

Tel +1.800.545.6258

Fax +1.800.527.5703

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Europe, Middle East,**

**Africa**

Tel +32.16.213.511

Fax +32.16.213.604

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

**Asia Pacific**

Tel +86.21.2412.1688

Fax +86.21.5426.3167

[cn.thermal.info@nvent.com](mailto:cn.thermal.info@nvent.com)

**Latin America**

Tel +1.713.868.4800

Fax +1.713.868.2333

[thermal.info@nvent.com](mailto:thermal.info@nvent.com)

Our powerful portfolio of brands:

**RAYCHEM PYROTENAX TRACER NUHEAT**