

Intelligent PDU, EN1xxx, 230 VAC, 1-PH

Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design



FEATURES

Enlogic EN1xxx Intelligent Power Distribution Units monitors input power of the entire PDU, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 230 VAC, 1-phase

C13, C19 outlets

SPECIFICATIONS

Table 1/6

Catalog Number	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EN1326	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN1325	Enlogic	Intelligent PDU	Socket Strip	(20) C13, (4) C19	24	Black
EN1330	Enlogic	Intelligent PDU	Socket Strip	(28) C13, (6) C19	34	Black
EN1335	Enlogic	Intelligent PDU	Socket Strip	(32) C13, (6) C19	38	Black
EN1337	Enlogic	Intelligent PDU	Socket Strip	(36) C13, (6) C19	42	Black

CatalogNumber	Product Family	Type	Product Type	Socket Type	SocketQuantity	Color
EN1350	Enlogic	Intelligent PDU	Socket Strip	(20) C13/C15, (20) C13/C15/C19/C 21	40	Black
EN1380	Enlogic	Intelligent PDU	Socket Strip	(16) Locking C13/C15, (16) Locking C13/C15/C19/C 21	32	Black

Table 2/6

Catalog Number	Circuit Breaker	Switched Outlets	Circuit Breaker Quantity	Power Rating	Input Cable Length	Input Cable Location
EN1326	No Circuit Breaker	No	0	3.7 kVA	3m	Top Feed
EN1325	16 A, 1-pole, Hy-Mag	No	2	7.4 kVA	3m	Top Feed
EN1330	16 A, 1-pole, Hy-Mag	No	2			Top Feed
EN1335	16 A, 1-pole, Hy-Mag	No	2			Top Feed
EN1337	16 A, 1-pole, Hy-Mag	No	2	7.4 kVA	3m	Top Feed
EN1350	20 A, 1-pole, Hy-Mag	No	2	7.4 kVA	3m	Top Feed
EN1380	20 A, 1-pole, Hy-Mag	No	2	7.4 kVA	3m	Top Feed

Table 3/6

Catalog Number	Input Voltage	Phase	Interrupt Rating	Nominal Voltage	Max Power Input	On/Off Switch Included
EN1326	100 – 240V	1 PH	5kAIC	230V	3.3 kVA	No
EN1325	200 – 240V	1 PH	5kAIC	230V	7.44 kVA	No
EN1330	200 – 240V	1 PH	5kAIC		7.44 kVA	
EN1335	200 – 240V	1 PH	5kAIC		7.44 kVA	

CatalogNumber	Input Voltage	Phase	InterruptRating	Nominal Voltage	Max Power Input	On/Off Switch Included
EN1337	200 – 240V	1 PH	5kAIC	230V	7.44 kVA	No
EN1350	200 – 240V	1 PH	5kAIC	230V	7.44 kVA	No
EN1380	200 – 240V	1 PH	5kAIC	230V	7.44 kVA	No

Table 4/6

Catalog Number	Amperage (Derated Amperage)	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable
EN1326	16 A	230VAC	0U	IEC 60309 316P6 (IP44)	Input	Yes
EN1325	32 A	230VAC	0U	IEC 60309 332P6 (IP44)	Input	No
EN1330	32 A	200 – 240VAC	0U	IEC 60309 332P6 (IP44)	Input	No
EN1335	32 A	200 – 240VAC	0U	IEC 60309 332P6 (IP44)	Input	No
EN1337	32 A	230VAC	0U	IEC 60309 332P6 (IP44)	Input	No
EN1350	32 A	230VAC	0U	IEC 60309 332P6 (IP44)	Input	No
EN1380	32 A	230VAC	0U	IEC 60309 332P6 (IP44)	Input	No

Table 5/6

Catalog Number	Material	Finish	Height	Width	Depth	Weight
EN1326	Steel	Powder Coated	1490mm	52mm	53mm	7.01kg
EN1325	Steel	Powder Coated	1490mm	52mm	53mm	7.1kg
EN1330						
EN1335						

CatalogNumber	Material	Finish	Height	Width	Depth	Weight
EN1337	Steel	Powder Coated	1750mm	52mm	53mm	8.12kg
EN1350	Steel	Powder Coated	1490mm	56mm	55mm	8.22kg
EN1380	Steel	Powder Coated	1490mm	56mm	55mm	8.02kg

Table 6/6

Catalog Number	Package Quantity	Quick Ship
EN1326	1	No
EN1325	1	No
EN1330	1	No
EN1335	1	No
EN1337	1	No
EN1350	1	No
EN1380	1	No

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE