

# MultipacPRO 19" Chassis, Aluminum, Perforated Top and Base



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have perforated top and bottom cover for better air flow and heat dissipation.

## CERTIFICATIONS

---



## FEATURES

---

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

## SPECIFICATIONS

---

<b>Material:</b>	Aluminum
<b>Finish:</b>	Anodized; Passivated
<b>Product Family:</b>	MultipacPRO
<b>EMC Shielding:</b>	No (Retrofittable)
<b>Type:</b>	Perforated

Table 1/2

Catalog Number	Rack Height	Depth	Usable Width	Mounting	Complies With	Certifications
20860-621	1U	220mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-105	RoHS
20860-622	1U	280mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-105	RoHS
20860-624	2U	220mm	403mm	Rack	IEC 60297-3-100	
20860-625	2U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-626	2U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-627	3U	280mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-628	3U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-629	3U	400mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-630	3U	460mm	403mm	Rack	IEC 60297-3-100	
20860-632	4U	340mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-633	4U	400mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-634	4U	460mm	403mm	Rack	IEC 60297-3-100	RoHS
20860-635	5U	460mm	403mm	Rack	IEC 60297-3-100	RoHS

Table 2/2

Catalog Number	Quick Ship
20860-621	No
20860-622	No

Catalog Number	Quick Ship
20860-624	No
20860-625	No
20860-626	No
20860-627	No
20860-628	No
20860-629	No
20860-630	No
20860-632	No
20860-633	No
20860-634	No
20860-635	No

## ADDITIONAL PRODUCT DETAILS

---

Please order front handles separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**