

# MultipacPRO 19" Chassis, Aluminum, Plain Top and Base



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have plain top and bottom cover.

## CERTIFICATIONS



## FEATURES

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

## SPECIFICATIONS

|                        |                      |
|------------------------|----------------------|
| <b>Material:</b>       | Aluminum             |
| <b>Finish:</b>         | Anodized; Passivated |
| <b>Product Family:</b> | MultipacPRO          |
| <b>EMC Shielding:</b>  | No (Retrofittable)   |
| <b>Type:</b>           | Solid                |

Table 1/2

| Catalog Number | Rack Height | Depth | Usable Width | Mounting | Complies With                    | Certifications |
|----------------|-------------|-------|--------------|----------|----------------------------------|----------------|
| 20860-601      | 1U          | 220mm | 403mm        | Rack     | IEC 60297-3-100, IEC 60297-3-105 | RoHS           |
| 20860-602      | 1U          | 280mm | 403mm        | Rack     | IEC 60297-3-100, IEC 60297-3-105 | RoHS           |
| 20860-603      | 1U          | 340mm | 403mm        | Rack     | IEC 60297-3-100                  |                |
| 20860-604      | 2U          | 220mm | 403mm        | Rack     | IEC 60297-3-100                  |                |
| 20860-605      | 2U          | 280mm | 403mm        | Rack     | IEC 60297-3-100                  | RoHS           |
| 20860-606      | 2U          | 340mm | 403mm        | Rack     | IEC 60297-3-100                  | RoHS           |
| 20860-607      | 3U          | 280mm | 403mm        | Rack     | IEC 60297-3-100                  | RoHS           |
| 20860-608      | 3U          | 340mm | 403mm        | Rack     | IEC 60297-3-100                  | RoHS           |
| 20860-609      | 3U          | 400mm | 403mm        | Rack     | IEC 60297-3-100                  | RoHS           |
| 20860-610      | 3U          | 460mm | 403mm        | Rack     | IEC 60297-3-100                  |                |
| 20860-611      | 4U          | 280mm | 403mm        | Rack     | IEC 60297-3-100                  |                |
| 20860-612      | 4U          | 340mm | 403mm        | Rack     | IEC 60297-3-100                  | RoHS           |
| 20860-613      | 4U          | 400mm | 403mm        | Rack     | IEC 60297-3-100                  | RoHS           |
| 20860-614      | 4U          | 460mm | 403mm        | Rack     | IEC 60297-3-100                  | RoHS           |
| 20860-615      | 5U          | 460mm | 403mm        | Rack     | IEC 60297-3-100                  | RoHS           |

Table 2/2

| Catalog Number | Quick Ship |
|----------------|------------|
|----------------|------------|

|           |    |
|-----------|----|
| 20860-601 | No |
| 20860-602 | No |
| 20860-603 | No |
| 20860-604 | No |
| 20860-605 | No |
| 20860-606 | No |
| 20860-607 | No |
| 20860-608 | No |
| 20860-609 | No |
| 20860-610 | No |
| 20860-611 | No |
| 20860-612 | No |
| 20860-613 | No |
| 20860-614 | No |
| 20860-615 | No |

## ADDITIONAL PRODUCT DETAILS

---

Please order front handles separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**