

# Varistar CP Flat Top Cover Closed

Flat top cover for Varistar CP cabinets without cable entry zones.



## FEATURES

Flat top cover closed

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Top Cover  
**Color Code:** RAL 7021  
**Material:** Steel

Table 1/2

| Catalog Number | Width | Depth | Protection Rating | Package Quantity | Color      | Finish        |
|----------------|-------|-------|-------------------|------------------|------------|---------------|
| 21630-260      | 600mm | 300mm | IP20              | 1                | Black Grey | Powder Coated |
| 21630-315      | 600mm | 300mm |                   | 1                | Black Grey | Powder Coated |
| 21630-254      | 600mm | 600mm | IP20              | 1                | Black Grey | Powder Coated |
| 21630-186      | 600mm | 600mm |                   | 1                | Black Grey | Powder Coated |
| 21630-255      | 600mm | 800mm | IP20              | 1                | Black Grey | Powder Coated |
| 21630-187      | 600mm | 800mm |                   | 1                | Black Grey | Powder Coated |

| CatalogNumber | Width | Depth  | Protection Rating | Package Quantity | Color      | Finish        |
|---------------|-------|--------|-------------------|------------------|------------|---------------|
| 21630-256     | 600mm | 900mm  | IP20              | 1                | Black Grey | Powder Coated |
| 21630-188     | 600mm | 900mm  |                   | 1                | Black Grey | Powder Coated |
| 21630-128     | 600mm | 1000mm | IP20              | 1                | Black Grey | Powder Coated |
| 21630-189     | 600mm | 1000mm |                   | 1                | Black Grey | Powder Coated |
| 21630-257     | 800mm | 600mm  | IP20              | 1                | Black Grey | Powder Coated |
| 21630-192     | 800mm | 600mm  |                   | 1                | Black Grey | Powder Coated |
| 21630-258     | 800mm | 800mm  | IP20              | 1                | Black Grey | Powder Coated |
| 21630-193     | 800mm | 800mm  |                   | 1                | Black Grey | Powder Coated |
| 21630-259     | 800mm | 900mm  | IP20              | 1                | Black Grey | Powder Coated |
| 21630-194     | 800mm | 900mm  |                   | 1                | Black Grey | Powder Coated |
| 21630-131     | 800mm | 1000mm | IP20              | 1                | Black Grey | Powder Coated |
| 21630-195     | 800mm | 1000mm |                   | 1                | Black Grey | Powder Coated |
| 21630-570     | 600mm | 300mm  |                   | 1                | Black Grey | Powder Coated |
| 21630-571     | 600mm | 600mm  |                   | 1                | Black Grey | Powder Coated |
| 21630-572     | 600mm | 800mm  |                   | 1                | Black Grey | Powder Coated |
| 21630-573     | 600mm | 900mm  |                   | 1                | Black Grey | Powder Coated |
| 21630-574     | 600mm | 1000mm |                   | 1                | Black Grey | Powder Coated |
| 21630-577     | 800mm | 600mm  |                   | 1                | Black Grey | Powder Coated |

| CatalogNumber | Width | Depth  | Protection Rating | Package Quantity | Color      | Finish        |
|---------------|-------|--------|-------------------|------------------|------------|---------------|
| 21630-578     | 800mm | 800mm  |                   | 1                | Black Grey | Powder Coated |
| 21630-579     | 800mm | 900mm  |                   | 1                | Black Grey | Powder Coated |
| 21630-580     | 800mm | 1000mm |                   | 1                | Black Grey | Powder Coated |
| 21630-557     | 600mm | 300mm  | IP55              | 1                | Black Grey | Powder Coated |
| 21630-558     | 600mm | 600mm  | IP55              | 1                | Black Grey | Powder Coated |
| 21630-559     | 600mm | 800mm  | IP55              | 1                | Black Grey | Powder Coated |
| 21630-560     | 600mm | 900mm  | IP55              | 1                | Black Grey | Powder Coated |
| 21630-561     | 600mm | 1000mm | IP55              | 1                | Black Grey | Powder Coated |
| 21630-564     | 800mm | 600mm  | IP55              | 1                | Black Grey | Powder Coated |
| 21630-565     | 800mm | 800mm  | IP55              | 1                | Black Grey | Powder Coated |
| 21630-566     | 800mm | 900mm  | IP55              | 1                | Black Grey | Powder Coated |
| 21630-567     | 800mm | 1000mm | IP55              | 1                | Black Grey | Powder Coated |
| 21630-129     | 600mm | 1100mm | IP20              | 1                | Black Grey | Powder Coated |
| 21630-190     | 600mm | 1100mm |                   | 1                | Black Grey | Powder Coated |
| 21630-130     | 600mm | 1200mm | IP20              | 1                | Black Grey | Powder Coated |
| 21630-191     | 600mm | 1200mm |                   | 1                | Black Grey | Powder Coated |
| 21630-196     | 800mm | 1100mm |                   | 1                | Black Grey | Powder Coated |
| 21630-132     | 800mm | 1100mm | IP20              | 1                | Black Grey | Powder Coated |

| CatalogNumber | Width | Depth  | Protection Rating | Package Quantity | Color      | Finish        |
|---------------|-------|--------|-------------------|------------------|------------|---------------|
| 21630-197     | 800mm | 1200mm |                   | 1                | Black Grey | Powder Coated |
| 21630-575     | 600mm | 1100mm |                   | 1                | Black Grey | Powder Coated |
| 21630-576     | 600mm | 1200mm |                   | 1                | Black Grey | Powder Coated |
| 21630-581     | 800mm | 1100mm |                   | 1                | Black Grey | Powder Coated |
| 21630-582     | 800mm | 1200mm |                   | 1                | Black Grey | Powder Coated |
| 21630-133     | 800mm | 1200mm | IP20              | 1                | Black Grey | Powder Coated |
| 21630-562     | 600mm | 1100mm | IP55              | 1                | Black Grey | Powder Coated |
| 21630-563     | 600mm | 1200mm | IP55              | 1                | Black Grey | Powder Coated |
| 21630-568     | 800mm | 1100mm | IP55              | 1                | Black Grey | Powder Coated |
| 21630-569     | 800mm | 1200mm | IP55              | 1                | Black Grey | Powder Coated |

Table 2/2

| Catalog Number | Type   | Works With  | Quick Ship |
|----------------|--------|-------------|------------|
| 21630-260      | Closed | Varistar CP | No         |
| 21630-315      | Closed | Varistar CP | No         |
| 21630-254      | Closed | Varistar CP | No         |
| 21630-186      | Closed | Varistar CP | No         |
| 21630-255      | Closed | Varistar CP | No         |
| 21630-187      | Closed | Varistar CP | No         |
| 21630-256      | Closed | Varistar CP | No         |

| Catalog Number | Type       | Works With  | Quick Ship |
|----------------|------------|-------------|------------|
| 21630-188      | Closed     | Varistar CP | No         |
| 21630-128      | Closed     | Varistar CP | No         |
| 21630-189      | Closed     | Varistar CP | No         |
| 21630-257      | Closed     | Varistar CP | No         |
| 21630-192      | Closed     | Varistar CP | No         |
| 21630-258      | Closed     | Varistar CP | No         |
| 21630-193      | Closed     | Varistar CP | No         |
| 21630-259      | Closed     | Varistar CP | No         |
| 21630-194      | Closed     | Varistar CP | No         |
| 21630-131      | Closed     | Varistar CP | No         |
| 21630-195      | Closed     | Varistar CP | No         |
| 21630-570      | Closed     | Varistar CP | No         |
| 21630-571      | Perforated | Varistar CP | No         |
| 21630-572      | Closed     | Varistar CP | No         |
| 21630-573      | Closed     | Varistar CP | No         |
| 21630-574      | Closed     | Varistar CP | No         |
| 21630-577      | Closed     | Varistar CP | No         |
| 21630-578      | Closed     | Varistar CP | No         |

| Catalog Number | Type   | Works With  | Quick Ship |
|----------------|--------|-------------|------------|
| 21630-579      | Closed | Varistar CP | No         |
| 21630-580      | Closed | Varistar CP | No         |
| 21630-557      | Closed | Varistar CP | No         |
| 21630-558      | Closed | Varistar CP | No         |
| 21630-559      | Closed | Varistar CP | No         |
| 21630-560      | Closed | Varistar CP | No         |
| 21630-561      | Closed | Varistar CP | No         |
| 21630-564      | Closed | Varistar CP | No         |
| 21630-565      | Closed | Varistar CP | No         |
| 21630-566      | Closed | Varistar CP | No         |
| 21630-567      | Closed | Varistar CP | No         |
| 21630-129      | Closed | Varistar CP | No         |
| 21630-190      | Closed | Varistar CP | No         |
| 21630-130      | Closed | Varistar CP | No         |
| 21630-191      | Closed | Varistar CP | No         |
| 21630-196      | Closed | Varistar CP | No         |
| 21630-132      | Closed | Varistar CP | No         |
| 21630-197      | Closed | Varistar CP | No         |

| Catalog Number | Type       | Works With  | Quick Ship |
|----------------|------------|-------------|------------|
| 21630-575      | Closed     | Varistar CP | No         |
| 21630-576      | Closed     | Varistar CP | No         |
| 21630-581      | Closed     | Varistar CP | No         |
| 21630-582      | Perforated | Varistar CP | No         |
| 21630-133      | Closed     | Varistar CP | No         |
| 21630-562      | Closed     | Varistar CP | No         |
| 21630-563      | Closed     | Varistar CP | No         |
| 21630-568      | Closed     | Varistar CP | No         |
| 21630-569      | Closed     | Varistar CP | No         |

## ADDITIONAL PRODUCT DETAILS

---

Please purchase the grounding kit separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**