

# Varistar CP Steel Door, Plain With 1-Point Locking



Varistar CP Steel Door, IP 20 with Single Point Locking.

## FEATURES

Steel door with single point locking for IP 20 protection class

Opening angle 180°

## SPECIFICATIONS

**Product Type:** Cabinet Door  
**Protection Rating:** IP20  
**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Height | Width | Locking Type         | Package Quantity | Color      |
|----------------|-------------|--------|-------|----------------------|------------------|------------|
| 21630-493      | 24U         | 1200mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-400      | 24U         | 1200mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-494      | 24U         | 1200mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-401      | 24U         | 1200mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-495      | 29U         | 1400mm | 600mm | Single Point Locking | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Locking Type         | Package Quantity | Color      |
|---------------|-------------|--------|-------|----------------------|------------------|------------|
| 21630-402     | 29U         | 1400mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-496     | 29U         | 1400mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-403     | 29U         | 1400mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-497     | 33U         | 1600mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-404     | 33U         | 1600mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-498     | 33U         | 1600mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-405     | 33U         | 1600mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-499     | 38U         | 1800mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-406     | 38U         | 1800mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-500     | 38U         | 1800mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-407     | 38U         | 1800mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-501     | 42U         | 2000mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-002     | 42U         | 2000mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-502     | 42U         | 2000mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-009     | 42U         | 2000mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-503     | 47U         | 2200mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-003     | 47U         | 2200mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-504     | 47U         | 2200mm | 800mm | Single Point Locking | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Locking Type         | Package Quantity | Color      |
|---------------|-------------|--------|-------|----------------------|------------------|------------|
| 21630-010     | 47U         | 2200mm | 800mm | Single Point Locking | 1                | Black Grey |
| 21630-004     | 52U         | 2450mm | 600mm | Single Point Locking | 1                | Black Grey |
| 21630-011     | 52U         | 2450mm | 800mm | Single Point Locking | 1                | Black Grey |

| Table 2/2      |            |                             |               |            |             |            |
|----------------|------------|-----------------------------|---------------|------------|-------------|------------|
| Catalog Number | Color Code | Complies With               | Finish        | Type       | Works With  | Quick Ship |
| 21630-493      | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-400      | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-494      | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-401      | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-495      | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-402      | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-496      | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-403      | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-497      | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-404      | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-498      | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-405      | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-499      | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |

| CatalogNumber | Color Code | Complies With               | Finish        | Type       | Works With  | Quick Ship |
|---------------|------------|-----------------------------|---------------|------------|-------------|------------|
| 21630-406     | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-500     | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-407     | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-501     | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-002     | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-502     | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-009     | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-503     | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-003     | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-504     | RAL 7021   | IEC 61587-1                 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-010     | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-004     | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |
| 21630-011     | RAL 7021   | IEC 61587-1,<br>IEC 61587-3 | Powder Coated | Steel Door | Varistar CP | No         |

## ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**