



# nVent CADDY Cat 425 Adjustable Cable Support with Pedestal Clamp



## CERTIFICATIONS



## FEATURES

Easy installation to pedestals used under raised floors

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Simple unlocking and locking of bar allows for additional cables to be added easily after installation

Adjustable strap allows for multiple support sizes to reduce inventory

Cost effective alternative to expensive cable tray

cULus® Listed and complies with NEC® and TIA requirements for structured cabling systems

Suitable for air handling spaces (plenum)

## SPECIFICATIONS


Table 1/2

| Catalog Number   | Article Number | Material               | Finish            | Diameter (Ø)   | Area                 | Cable Capacity, Cat 5e |
|------------------|----------------|------------------------|-------------------|----------------|----------------------|------------------------|
| CAT425WMCD1<br>B | 181881         | Steel,<br>Polyethylene | Electrogalvanized | 100 mm, 150 mm | 13181mm <sup>2</sup> | 425                    |

Table 2/2

| Catalog Number | Article Number | Cable Capacity,<br>Cat 6 | Cable Capacity,<br>Cat 6A | Pedestal Size                            | Static Load |
|----------------|----------------|--------------------------|---------------------------|------------------------------------------|-------------|
| CAT425WMCD1B   | 181881         | 325                      | 210                       | 19 mm Square,<br>22.2 - 28.5 mm<br>Round | 220N        |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

