

LHX+ Air/Liquid Heat Exchanger 115 V UL

Data Solutions



FEATURES

19" mountable Air/liquid heat exchanger with fan

Easy replaceable fans without dismounting the heat exchanger

Coolant feed from top or bottom

UL Certified

SPECIFICATIONS

Depth: 500mm
Product Type: Air/Liquid Heat Exchanger
Airflow Direction: Front to Top

Table 1/2

Catalog Number	Fan Quantity	Input Voltage AC	Package Quantity	Supply Voltage	Redundant Power Supply	Coolant Feed
29714-036	1	100 – 115V	1	115V min	No	Bottom
29714-027	1	100 – 115V	1	115V min	No	Bottom
29714-022	2	100 – 115V	1	115V min	No	Bottom

CatalogNumber	Fan Quantity	Input Voltage AC	Package Quantity	Supply Voltage	Redundant Power Supply	Coolant Feed
29714-033	2	100 – 115V	1	115V min	No	Bottom

Table 2/2

Catalog Number	Height	Product Family	Width	Works With
29714-036	266mm	Cooling	426mm	Varistar, Varistar CP
29714-027	266mm	Cooling	426mm	Varistar, Varistar CP
29714-022	266mm	Cooling	426mm	Varistar, Varistar CP
29714-033	266mm	Cooling	426mm	Varistar, Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order separatly: Monitoring via Control unit, water control package, display and door contact switch.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE