

# Rack Panel for 19-in. Racks

## Data Solutions



The Rack Panel is used to cover unused rack space in cabinets or open frame racks for a finished appearance. It can also be used for surface mounting small devices. Panels are flat with mounting slots spaced at 19-inch EIA standard spacing. Please note the mounting hardware is sold separately.

### FEATURES

The Rack Panel is used to cover unused rack space in cabinets or open frame racks for a finished appearance

It can also be used for surface mounting mall devices

Panels are flat with mounting slots spaced at 19-inch EIA standard spacing

Mounting hardware is sold separately

### SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
P19RPP1UB	13753	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm
P19RPP2UB	13754	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm
P19RPP3UB	13755	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm
P19RPP4UB	13756	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm
P19RPP5UB	13757	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm

CatalogNumber	Article Number	Material	Finish	Color	Color Code	Thickness
P19RPP6UB	13758	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm

Table 2/2

Catalog Number	Article Number	Rack Units
P19RPP1UB	13753	1U
P19RPP2UB	13754	2U
P19RPP3UB	13755	3U
P19RPP4UB	13756	4U
P19RPP5UB	13757	5U
P19RPP6UB	13758	6U

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**