

# Telescopic Slides C-Profile for Cabinet

## Data Solutions



Telescopic slides with guiding profile for fitting in cabinets with 25 kg load capacity.

## CERTIFICATIONS



## FEATURES

For mounting 84 HP wide subracks in the 19" plane

Loading capacity: 25 kg per pair

The guiding profile (1) is matched to the fixing dimension in the cabinet (it is bolted to the 19" profile of the cabinet); the adaptor Rail (3) is matched to the depth and fixing dimension on the subrack (it is inserted into the guiding profile like a telescopic slide)

## SPECIFICATIONS

<b>Material:</b>	Aluminum
<b>Finish:</b>	Anodized
<b>Type:</b>	C Profile
<b>Product Type:</b>	Telescopic Slide

Table 1/1

Catalog Number	Depth	Package Quantity
----------------	-------	------------------

24562-473	1200mm	2
24562-446	250mm	2
24562-449	600mm	2
24562-451	800mm	2
24562-452	900mm	2
24562-460	500mm	2
24562-461	600mm	2
24562-464	600mm	2
24562-466	800mm	2
24562-467	900mm	2
24562-468	1000mm	2
24562-472	1100mm	2
24562-474	800mm	2

## ADDITIONAL PRODUCT DETAILS

---

No protection against extraction, no stop at full extension.

The reinforcement Rail and the C-Rails have been tested in accordance with the Russian atomic energy authority GAN standards.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**