

Cathodic Protection Adapter Sleeve



FEATURES

Used to build up smaller cathodic protection conductors for a proper fit into the required nVent ERICO Cadweld mold

SPECIFICATIONS

Material: Copper

Table 1/1

Catalog Number	Type	Length (L)	Thickness (T)	Diameter (Ø)
CAB112	Straight	26.99mm	0.79 mm	5.38 mm
CAB1331H	Straight	25.4mm	0.64 mm	2.69 mm
CAB1331K	Straight	25.4mm	0.79 mm	3.56 mm
CAB1331L	Straight	25.4mm	0.79 mm	4.32 mm
CAB1331V	Straight	25.4mm	0.79 mm	6.1 mm
CAS03F	Flared	25.4mm	0.79 mm	11.56 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE