

Compression Coupler for Stainless Steel Ground Rod, Pointed



CERTIFICATIONS





FEATURES

Threadless compression coupler for use with pointed stainless steel ground rods in corrosive soils

Inside of coupler is tapered so ground rod compresses during installation to form an irreversible conductive connection

SPECIFICATIONS

Material: Stainless Steel 304 (EN 1.4301)

| Table 1/1 | | | |
|----------------|---------------------------------|------------|-------------|
| Catalog Number | Ground Rod Diameter, Nominal | Length (L) | Unit Weight |
| CC58SS | 5/8" | 76.2mm | 0.11 kg |
| CC34SS | 3/4" | 82.6mm | 0.15 kg |



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY TRACHTE ERICO HOFFMAN ILSCO SCHROFF