

Conductor Insulation Stripping Tool, 4 x 4



FEATURES

Provides precision stripping with no conductor damage

Strips quickly, even in cold climates

Guarded cutting blades ensure safety

Bushings change easily with supplied hex wrench

SPECIFICATIONS

Length 1 (L1): 114 mm


Length 2 (L2): 127 mm

Material: Aluminum;Steel

Table 1/1

Catalog Number	Bushing A	Bushing B	Bushing C	Bushing D
SBRT360001004	3/16" Bondstrand, 4/64" Insulation	#6 Sol, 11/64" Insulation	#6 Sol, 12/64" Insulation	3/16" Bondstrand, 6/64" Insulation
SBRT36000906	3/16" Bondstrand, 4/64" Insulation	#6 Sol, 11/64" Insulation	#6 Sol, 12/64" Insulation	#9 Sol, 10/64" Insulation
SBRT360001010	3/16" Bondstrand, 6/64" Insulation	3/16" Bondstrand, 6/64" Insulation	#6 Sol, 11/64" Insulation	#6 Sol, 12/64" Insulation
SBRT360002132	#6 Sol, 6/64" Insulation	#4 Str, 6/64" Insulation	#9 Sol, 5/64" Insulation	3/16" Bondstrand, 6/64" Insulation

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE