

Cable to Web of Rail Mold Only, Signal, 1" Tab Bond Terminal Style, 3/16" Bondstrand, Left Hand

CATALOG NUMBER

SBB200CLH



FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

PRODUCT ATTRIBUTES

Material: Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: 1" Tab

Conductor Size: 3/16" Bondstrand

Conductor Outer Diameter, Nominal: 4.76mm

Welder Style: TB5;T21

Orientation: Left Hand

Mold Only: Yes

Welding Material: SB25, Sold Separately

Conductor Sleeve: SBS12C, Sold Separately

Bond Clip: S2659, Sold Separately

Hammer Die: SBD50, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE