

# **Industrial Stack Pinch-Close Cable Fastener**



## **CERTIFICATIONS**





## **FEATURES**

Provides threaded attachment point for lightning conductors

# **SPECIFICATIONS**


Material: Brass

Conductor Size, UL: Class 2 (4/0 Max)

Table 1/2							
Catalog Number	Finish	Thread Size (TS)	Screw Length (L)	Height (H)	Width (W)	Unit Weight	
LPC481SH	Bare	1/2" UNC	22.23mm	22.86 mm	34.54 mm	0.08 kg	
LPC481LG	Bare	1/2" UNC	38.1mm	22.86 mm	34.54 mm	0.1 kg	
LPLC481SH	Lead Covered	1/2" UNC	22.23mm	22.86 mm	34.54 mm	0.26 kg	
LPLC481LG	Lead Covered	1/2" UNC	38.1mm	22.86 mm	34.54 mm	0.28 kg	

Table 2/2				
Catalog Number	Certifications			
LPC481SH	E202878-Combined_CoC, E202878-Combined_CoC			
LPC481LG	E202878-Combined_CoC, E202878-Combined_CoC			
LPLC481SH				
LPLC481LG				

## **DIAGRAMS**



# **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

 $^{\triangle}$  WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

## **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE