

# **Triggered Spark Gap**



#### **FEATURES**

Triggering air gap technology provides low let-through voltage, which offers superior protection compared to traditional spark gaps

Effective equipotential bonding provides N-PE equalization protection bond on TT power distribution systems

## **SPECIFICATIONS**

Catalog Number	TSG11302S
Nominal System Voltage (Un)	240 VAC
Max Continuous Operating Voltage (Uc)	440 VAC
Voltage Protection Level (Up)	1500 V @ 3 kA 2300 V @ 20 kA
Max Discharge Current (Imax)	130 50
Follow Current Extinguishing Capability @ Un	43kA
Impulse Current (limp)	50kA 10/350 μs
Max Operating Current	2.2 mA
Protection Modes	Single
Technology	Triggered Spark Gap
Frequency	50 - 60 Hz
Enclosure Material	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20 NEMA®-1

Catalog Number	TSG11302S
Mounting	35 mm top hat DIN rail
Status Indication	LED for line connected modes
Temperature	-40 to 80 °C
Module Width	2 M
Depth (D)	68mm
Height (H)	90 mm
Width (W)	36 mm
Unit Weight	0.3 kg
Complies With	IEC® 61643-1 Class I, Class II ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 μs, 10 kA 10/350 μs

## ADDITIONAL PRODUCT DETAILS

TSG11302SNE used for L-PE Mode; TSG11302S and TSG11302S120V used for L-N due to follow current control.

## **DIAGRAMS**



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### **Europe**

Germany: 800 1890272 Other Countries: +31 13 5835404

#### **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE